

Adapter plate


ISAP-S4 195x195x11

Part no.:10.01.14.00231

<https://www.schmalz.com/10.01.14.00231>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Systems from SCM / Morbidelli > Adapter-Plates ISAP-S > ISAP-S4 195x195x11

Adapter-Plate Innospann for SCM/Morbidelli console - Type 4




Length L: 195 mm

Width B: 195 mm

Height H: 11 mm

Design Data



Attribute	Value
B	195 mm
B1	145 mm
H	11 mm
H1	28 mm
L	195 mm
L1	145 mm

Technical Data

Attribute	Value
Weight	0.36 kg

Accessories

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Adapter plate

ISAP-S4 195x195x11

Part no...:10.01.14.00231

<https://www.schmalz.com/10.01.14.00231>



ISCUP Cup 1 80x80x16

Part no...:10.01.15.00209

Dimensions (LxB): 80 x 80

Length L: 80 mm

Width B: 80 mm

Height H: 16 mm



ISCUP Cup 2 80x40x16

Part no...:10.01.15.00210

Dimensions (LxB): 80 x 40

Length L: 80 mm

Width B: 40 mm

Height H: 16 mm



ISCUP Cup 3 80x28x16

Part no...:10.01.15.00211

Dimensions (LxB): 80 x 28

Length L: 80 mm

Width B: 28 mm

Height H: 16 mm

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Adapter plate

ISAP-S4 195x195x11

Part no...:10.01.14.00231

<https://www.schmalz.com/10.01.14.00231>



ISMB 80x80x8

Part no...:10.01.15.00188

Dimensions (LxB): 80x80

Basic area: 80 x 80 mm

Length L: 80 mm

Width B: 80 mm

Height H: 8 mm



ISZR-V 80x15

Part no...:10.01.15.00052

External diameter D: 80 mm

Internal diameter d: 60 mm

Height H: 15 mm

Spare parts



ISMST 19-7 4ISMST

Part no...:10.01.14.00847

External diameter D: 7 mm

Height H: 11.5 mm

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Adapter plate

ISAP-S4 195x195x11

Part no...:10.01.14.00231

<https://www.schmalz.com/10.01.14.00231>




ISZR-V 80x15

Part no...:10.01.15.00052

External diameter D: 80 mm

Internal diameter d: 60 mm

Height H: 15 mm



VCDR 141x77.2x5.1 VCBL-S

Part no...:10.01.12.03138


Length L: 141 mm

Width B: 77.2 mm

Height H: 5.1 mm

Construction use: Vacuum block VCBL-S

Clamping range: mm



VST VCBL-S DI-RA

Part no...:10.01.12.03318

Construction use: Vacuum block VCBL-S

Clamping range: mm