

Cup

ISCUP Cup 2 80x40x16

Part no...:10.01.15.00210

<https://www.schmalz.com/10.01.15.00210>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Innospann Clamping Equipment ISCUP/ISMB/ISQB > ISCUP Cup 2 80x40x16

Suction cup for Innospann




Dimensions (LxB): 80 x 40

Length L: 80 mm

Width B: 40 mm

Height H: 16 mm

Design Data



Attribute	Value
B	40 mm
d	60 mm
H	16 mm
L	80 mm

Technical Data

Attribute	Value
Weight	0.07 kg

Spare parts

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Cup

ISCUP Cup 2 80x40x16

Part no...:10.01.15.00210

<https://www.schmalz.com/10.01.15.00210>



O-RING 48x2 CR-70

Part no...:10.07.08.00468



DI-PROF 4x10 MOS EPDM HR

Part no...:10.01.15.00062

Width B: 4 mm

Height H: 10 mm

Sealing material: EPDM

Material type: Foam rubber

Form: half-round



ISDR 81x43x12 Cup 2 NK-50

Part no...:10.01.15.00021

Width B: 43 mm

Height H: 12 mm

Length L: 81 mm

Suction cup material: Natural rubber NK-50

Type: Cup 2

Cup

ISCUP Cup 2 80x40x16

Part no...:10.01.15.00210

<https://www.schmalz.com/10.01.15.00210>



ISRPL 66x26x8.5

Part no...:10.01.15.00018

Width B: 26 mm

Height H: 8.5 mm

Length L: 66 mm

Type: Cup 2