

Holder tooling suction Cup

HT-SG A3 I 10 31 G3/8-AG AB

Part no...:10.07.06.00356

<https://www.schmalz.com/10.07.06.00356>

Home > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Holder System for Tooling HT > Holders for Suction Cups HT-SG I > HT-SG A3 I 10 31 G3/8-AG AB

Holder for suction cup



Connection 1: Ball head 28.5 mm


Shape: integrated nozzle

Suction cup connection: G3/8"-M

Vacuum connection: G1/8"-F

Add. function: Active blowing off

Design Data



Attribute	Value
B	31 mm
B1	73 mm
B2	32 mm
D	28.50 mm
G2	G3/8"-M
G3	G1/8"-F
G4	G1/8"-F
H	24.50 mm
H1	63.80 mm
L	45.50 mm
L1	80 mm
L2	67 mm
L3	13 mm
LG2	22 mm
SW1	22 mm

Technical Data

Attribute	Value
Weight	162.70 g
Product family	HT-SG-I

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Holder tooling suction Cup

HT-SG A3 I 10 31 G3/8-AG AB

Part no.:10.07.06.00356

<https://www.schmalz.com/10.07.06.00356>

Accessories



STV-GE G1/8-AG 6

Part no.:10.08.02.00204

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 11.4 mm

Length L: 16.4 mm



STV-W G1/8-AG 6

Part no.:10.08.02.00288

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Plastics

Operating temperature: °C

Length L: 20.8 mm