

## Holder tooling suction Cup

HT-SG A2 I 10 31 G3/8-AG AV VS

Part no.:10.07.06.00590

<https://www.schmalz.com/10.07.06.00590>

Home > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Holder System for Tooling HT > Holders for Suction Cups HT-SG I > HT-SG A2 I 10 31 G3/8-AG AV VS

### Holder for suction cup




Connection 1: Bolt with slot  $\varnothing 19\text{mm}$

Shape: integrated nozzle

Suction cup connection: G3/8"-M

Add. function: Atmospheric ventilation

### Design Data



| Attribute | Value    |
|-----------|----------|
| B         | 31 mm    |
| B1        | 80.40 mm |
| B2        | 32 mm    |
| D         | 19 mm    |
| G2        | G3/8"-M  |
| G4        | G1/8"-F  |
| H         | 24.50 mm |
| H1        | 59.90 mm |
| L         | 39.30 mm |
| L1        | 82.55 mm |
| L2        | 60.80 mm |
| L3        | 11.70 mm |
| LG2       | 22 mm    |
| SW1       | 22 mm    |

### Technical Data

| Attribute      | Value    |
|----------------|----------|
| Weight         | 225.60 g |
| Product family | HT-SG-I  |

### Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | [info@schmalz.si](mailto:info@schmalz.si)

## Holder tooling suction Cup

HT-SG A2 I 10 31 G3/8-AG AV VS

Part no.:10.07.06.00590

<https://www.schmalz.com/10.07.06.00590>

### Accessories



#### STV-GE G1/8-AG 6

Part no.:10.08.02.00204

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 11.4 mm

Length L: 16.4 mm



#### STV-W G1/8-AG 6

Part no.:10.08.02.00288

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Plastics

Operating temperature: °C

Length L: 20.8 mm