


Compact ejector with Condition Monitoring, power blow-off function and pneu. air-saving function



|                                                      |
|------------------------------------------------------|
| Nozzle diameter: 3 mm                                |
| Electrical connection: Male connect M12, 5 pol       |
| Suction rate (max.): 220 l/min                       |
| Air consumption suction: 380 l/min                   |
| Pressure range (operating pressure): 3.0 ... 6.0 bar |
| Max. vacuum: -850 mbar                               |
| Control valve: Normally closed                       |
| Function: Pressure Control                           |
| Protection type IP: IP 65                            |
| Sound level free: 72 dB(A)                           |
| Communication: IO-Link (Class B)                     |

Design Data



| Attribute | Value    |
|-----------|----------|
| B         | 39 mm    |
| B2        | 6.80 mm  |
| d         | 5.50 mm  |
| G1        | G3/8"-F  |
| G2        | M12x1-M  |
| G3        | M5-F     |
| H         | 108 mm   |
| H1        | 160 mm   |
| H2        | 54 mm    |
| H3        | 6 mm     |
| H4        | 26 mm    |
| L         | 210 mm   |
| L2        | 5 mm     |
| L3        | 97 mm    |
| L4        | 35.50 mm |
| X1        | 89 mm    |
| X2        | 42 mm    |
| Y1        | 10 mm    |
| Y2        | 24 mm    |

## Schmalz X-Pump

SXMPi 30 NC H PC M12-5

Part no...:10.02.02.05298

<https://www.schmalz.com/10.02.02.05298>

### Technical Data

| Attribute                                     | Value           |
|-----------------------------------------------|-----------------|
| Nozzle diameter                               | 3 mm            |
| Degree of evacuation                          | 85 %            |
| Suction rate (max.)                           | 220 l/min       |
| Suction rate (max.)                           | 13.20 m³/h      |
| Suction rate (max.)                           | 7.77 cfm        |
| Air consumption suction                       | 380 l/min       |
| Air consumption suction                       | 13.42 cfm       |
| Air consumption suction                       | 22.80 m³/h      |
| Sound level free                              | 72 dB(A)        |
| Pressure range (operating pressure)           | 3.0 ... 6.0 bar |
| Pressure range (operating pressure)           | 43.5 ... 87.0   |
| Max. air consumption blow off                 | 320 l/min       |
| Recomm. internal hose diameter compressed air | 8 mm            |
| Recomm. internal hose diameter vacuum         | 9 mm            |
| Control valve                                 | Normally closed |
| Weight                                        | 0.91 kg         |
| Operating temperature                         | 0 ... 50 °C     |
| Product family                                | SXMPi           |

### Accessories



#### ASK B-M12-5 5000 S-M12-5

Part no...:21.04.05.00266

Cable length: 5,000 mm

Material hose: PUR cable

### Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | [info@schmalz.si](mailto:info@schmalz.si)

## Schmalz X-Pump

SXMPi 30 NC H PC M12-5

Part no.:10.02.02.05298

<https://www.schmalz.com/10.02.02.05298>



### ASK B-M12-5 2000 S-M12-5

Part no.:21.04.05.00211

Pressure range (operating pressure): bar

Electrical connection: Fem connect M12, 5 pol

Cable length: 2,000 mm

Material hose: PUR cable



### ASK B-M12-5 5000 K-5P

Part no.:21.04.05.00080

Electrical connection: Fem connect M12, 5 pol

Cable length: 5,000 mm

Material hose: PUR cable