

## Flat suction cup (round)

PFG 20 NBR-ESD-55 N006

Part no.:10.01.01.13786

<https://www.schmalz.com/10.01.01.13786>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > PFG 20 NBR-ESD-55 N006

### Flat suction cup (round) for smooth or slightly rough surfaces




Size: 20

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

### Design Data



| Attribute  | Value    |
|------------|----------|
| d          | 4.50 mm  |
| d1         | 11 mm    |
| Dk         | 15.20 mm |
| Dmax(S)    | 23 mm    |
| Ds         | 20 mm    |
| H          | 10 mm    |
| H2         | 4.50 mm  |
| Z (Stroke) | 2.20 mm  |

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

### Technical Data

| Attribute                   | Value                  |
|-----------------------------|------------------------|
| Suction force (-600mbar)    | 15.50 N                |
| Volume                      | 0.86 cm <sup>3</sup>   |
| Curve radius (min) (convex) | 20 mm                  |
| Size                        | 20                     |
| Nipple family               | N 006                  |
| Suction cup material        | Nitrile rubber NBR-ESD |
| Material hardness [Shore A] | 55 Shore A             |

### Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | [info@schmalz.si](mailto:info@schmalz.si)

## Flat suction cup (round)

PFG 20 NBR-ESD-55 N006

Part no.:10.01.01.13786

<https://www.schmalz.com/10.01.01.13786>

Product family

PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor  
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

### Accessories



#### SA-NIP N006 G1/8-AG DN200

Part no.:10.01.01.03530

Thread G1: G1/8"-M

Length L1: 19.5 mm

Fitting length: 5 mm

Material: Aluminum



#### SA-NIP N006 G1/8-IG DN200

Part no.:10.01.01.03522

Thread G1: G1/8"-F

Length L1: 22.5 mm

Fitting length: 16 mm

Material: Aluminum

### Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | [info@schmalz.si](mailto:info@schmalz.si)