

Flat suction cup (round)

PFG 2 SI-CO-55 N003

Part no...:10.01.01.10050

<https://www.schmalz.com/10.01.01.10050>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > PFG 2 SI-CO-55 N003

Flat suction cup (round) for smooth or slightly rough surfaces




Size: 2

Suction cup material: Silicone SI conductive

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d	2 mm
d1	3 mm
Dk	4.20 mm
Dmax(S)	3 mm
Ds	2 mm
H	4 mm
H2	1.50 mm
H3	2.50 mm
Z (Stroke)	0.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	0.12 N
Volume	0.01 cm ³
Curve radius (min) (convex)	2 mm
Size	2
Nipple family	N 003
Suction cup material	Silicone SI conductive
Material hardness [Shore A]	55 Shore A
Weight	0.10 g

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | schmalz@schmalz.com.tr

Flat suction cup (round)

PFG 2 SI-CO-55 N003

Part no...:10.01.01.10050

<https://www.schmalz.com/10.01.01.10050>

Product family

PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SA-NIP N003 M3-AG DN100

Part no...:10.01.01.00316

Thread G1: M3-M

Length L1: 7.5 mm

Fitting length: 2 mm

Material: Aluminum

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | schmalz@schmalz.com.tr