

Flat suction pad (round)

SFF 40 EPDM-45 G1/4-AG

Part no.:10.01.01.14270

<https://www.schmalz.com/10.01.01.14270>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Suction Cups SFF / SFB1 > SFF 40 EPDM-45 G1/4-AG

Flat suction cup (round) for dynamic handling of thin and flexible workpieces




Size: 40

Suction cup material: EPDM

Material hardness [Shore A]: 45 Shore A

Design Data



Attribute	Value
Dmax(S)	42 mm
Ds	40 mm
dn	4 mm
G1	G1/4-AG
LG1	10 mm
H	26.20 mm
SW1	17 mm
Z (Stroke)	2.70 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	48.60 N
Volume	4.30 cm ³
Size	40
Number of folds	0
Suction cup material	EPDM
Material hardness [Shore A]	45 Shore A
Weight	17.70 g
Product family	SFF

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | schmalz@schmalz.com.tr

Flat suction pad (round)

SFF 40 EPDM-45 G1/4-AG

Part no...:10.01.01.14270

<https://www.schmalz.com/10.01.01.14270>

Spare parts



SFF 40 EPDM-45 SC050

Part no...:10.01.01.14049

Size: 40

Suction cup material: EPDM

Material hardness [Shore A]: 45 Shore A

Number of folds: 0



SC 050 G1/4-AG SW410

Part no...:10.01.06.04347

Connection geometry: 050

Vacuum connection: G1/4"-M

Fitting length: 7.2 mm

Nominal diameter dn: 4.1 mm

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | schmalz@schmalz.com.tr