


Flexible suction cup mounting for adaptation to sloping surfaces



Thread G1: G1/4"-M
Thread G2: G1/4"-M
Operating temperature: 0 ... 70 °C

Design Data



Attribute	Value
dn	3 mm
G1	G1/4"-M
G2	G1/4"-M
L	16.50 mm
LG1	10.50 mm
LG2	12 mm
SW1	17 mm
W	12 °

Technical Data

Attribute	Value
Bending moment	10 Nm
Vertical load	750 N
Weight	30 g
Product family	FLK