

Bellows suction pad (round)

SFB1 10 EPDM-45 SC030

Part no...:10.01.06.04373

<https://www.schmalz.com/10.01.06.04373>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > SFB1 10 EPDM-45 SC030

Bellows suction cup (round) with 1.5 corr. for dynamic handling workpieces




Size: 10

Suction cup material: EPDM

Material hardness [Shore A]: 45 Shore A

Number of folds: 1.5

Design Data



Attribute	Value
D1	8.20 mm
Dmax(S)	11 mm
Dk	8.70 mm
Ds	10 mm
d	5.50 mm
d1	7.30 mm
d2	3.40 mm
H	12.30 mm
H2	4.20 mm
Z (Stroke)	2.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	0.50 N
Volume	0.29 cm ³
Size	10
Number of folds	1.50
Suction cup material	EPDM
Material hardness [Shore A]	45 Shore A
Curve radius (min) (convex)	10 mm
Nipple family	SC 030

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | schmalz@schmalz.com.tr

Bellows suction pad (round)

SFB1 10 EPDM-45 SC030

Part no.:10.01.06.04373

<https://www.schmalz.com/10.01.06.04373>

Product family

SFB1

Accessories



SC 030 M5-AG

Part no.:10.01.06.02802

Connection geometry: 030

Connection: M5-M

Length L1: 15.5 mm

Fitting length: 5 mm

Nominal diameter dn: 1.8 mm

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | schmalz@schmalz.com.tr