

Bell suction cup (oval)

SAOXM 60x20 ED-85 G1/4-IG

Part no...:10.01.24.00013

<https://www.schmalz.com/10.01.24.00013>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bell-Shaped Suction Cups SAOXM (Oval) > SAOXM 60x20 ED-85 G1/4-IG

High-Speed bell shaped suction cup for (oval) very dynamic handling of smooth and oily workpieces



Suction cup material: Elastodur ED


Material hardness [Shore A]: 85 Shore A

Nipple material: Aluminum

Connection: G1/4-IG

Add. function: Friction disc

Design Data



Attribute	Value
Bmax(S)	24 mm
Bs	18.70 mm
dn	5.10 mm
G1	G1/4"-F
H	38.50 mm
LG1	12 mm
Lmax(S)	67 mm
Ls	61.80 mm
SW1	17 mm
SW3	5 mm
Z (Stroke)	4.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	56 N
Lateral force	44 N
Lateral force (oily surface)	62 N
Volume	5 cm ³
Curve radius (min) (convex)	10 mm
Hose diameter (rec.) d	4 mm

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0123 | schmalz@schmalz.com.tr

Bell suction cup (oval)

SAOXM 60x20 ED-85 G1/4-IG

Part no...:10.01.24.00013

<https://www.schmalz.com/10.01.24.00013>

Dimensions (LxB)	60 x 20
Suction cup material	Elastodur ED
Material hardness [Shore A]	85 Shore A
Weight	25.30 g
Product family	SAOXM

Spare parts




SAOXM 60x20 ED-85 SC045-AR

Part no...:10.01.24.00001

Dimensions (LxB): 60 x 20

Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A



SC-I 045 AR-FDC

Part no...:10.01.24.00009

Size: 45

Shape: Anti Rot / Friction Elem

Use: SAOXM 60x20

Contact Schmalz


Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0123 | schmalz@schmalz.com.tr

Bell suction cup (oval)

SAOXM 60x20 ED-85 G1/4-IG

Part no...:10.01.24.00013

<https://www.schmalz.com/10.01.24.00013>



SC-A 045-AR G1/4-IG L

Part no...:10.01.06.03130

Connection geometry: 045-AR

Thread G1: G1/4"-F

Length L: 17.2 mm

Shape: Self Locking



SC-S 045 L

Part no...:10.01.06.02740

Size: 45

Shape: Self Locking



SAOXM 60x20 ED-85 SC045-AR

Part no...:10.01.24.00001

Dimensions (LxB): 60 x 20

Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 310 0123 | schmalz@schmalz.com.tr