

Bellows suction cup (round)

SPB4 40 SI-55 G1/4-AG

Part no...:10.01.06.03526

<https://www.schmalz.com/10.01.06.03526>

Home > Vacuum Technology for Automation > Vacuum Components > Area Gripping Systems and End Effectors > Vacuum End Effectors VEE > Suction Cups for Vacuum End Effectors > SPB4 40 SI-55 G1/4-AG

Bellows suction cup (round) for very uneven workpieces



Size: 40


Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Thread G1: G1/4"-M

Number of folds: 4.5

Design Data



Attribute	Value
d2	23 mm
dn	8 mm
Dmax(S)	41.50 mm
Ds	40.50 mm
G1	G1/4"-M
H	73.10 mm
LG1	10 mm
SW1	27 mm
Z (Stroke)	27 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	25 N
Pull-off force	39 N
Volume	35.74 cm ³
Hose diameter (rec.) d	12 mm
Number of folds	4.50
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A
Size	40

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 01 23 | schmalz@schmalz.com.tr

Bellows suction cup (round)

SPB4 40 SI-55 G1/4-AG

Part no...:10.01.06.03526

<https://www.schmalz.com/10.01.06.03526>

Weight	40.70 g
Product family	SPB4

Accessories



SIEB 19.5x1 MS-A2 103

Part no...:10.07.01.00321

External diameter D: 19.5 mm
Length L: 1 mm
Material: Brass / Stainless steel
Filter pore size: 103 µm



SSB 20-32 ST-VZ

Part no...:10.07.10.00003

Clamping range: 20.0 ... 32.0 mm
Material: Steel
Surface: galvanised



SPI 32 PE SPB4-40

Part no...:10.01.06.02856

Size: 32
Material: Polyethylene
Use: SPB4-40

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0123 | schmalz@schmalz.com.tr

Bellows suction cup (round)

SPB4 40 SI-55 G1/4-AG

Part no...:10.01.06.03526

<https://www.schmalz.com/10.01.06.03526>



SPSE 40

Part no...:10.01.06.02954

Size: 40

Spare parts



SC 090 G1/4-AG

Part no...:10.01.06.02793

Connection geometry: 090

Vacuum connection: G1/4"-M

Length L1: 33.5 mm

Fitting length: 7.5 mm

Nominal diameter dn: 8 mm



SPB4 40 SI-55 SC090

Part no...:10.01.06.02590

Size: 40

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Number of folds: 4.5

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 310 0123 | schmalz@schmalz.com.tr