

## Plug union, elbow

STV-WF G1/8-AG 10

Part no.:10.08.02.00257

<https://www.schmalz.com/10.08.02.00257>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STV-WF G1/8-AG 10

### Push-in Fitting, swivelling and lockable



Thread G1: G1/8"-M


Hose diameter: 10 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 25.2 mm

### Design Data



| Attribute | Value    |
|-----------|----------|
| d         | 10 mm    |
| G1        | G1/8"-M  |
| dn        | 10 mm    |
| D1        | 16.70 mm |
| H         | 9.80 mm  |
| H1        | 23.60 mm |
| L         | 25.20 mm |
| L1        | 33.60 mm |
| LG1       | 5 mm     |
| SW1       | 14 mm    |
| SW3       | 17 mm    |

### Technical Data

| Attribute                           | Value               |
|-------------------------------------|---------------------|
| Hose type                           | Hose D = 10 d = 7   |
| Hose type                           | 10-7                |
| Material                            | Nickel plated       |
| Pressure range (operating pressure) | -0.95 ... 15.00 bar |
| Operating temperature               | -10 ... 70 °C       |
| Weight                              | 49 g                |

### Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | [schmalz@schmalz.com.tr](mailto:schmalz@schmalz.com.tr)

## Plug union, elbow

STV-WF G1/8-AG 10

Part no.:10.08.02.00257

<https://www.schmalz.com/10.08.02.00257>

Product family

STV

### Accessories



#### VSL 10-7 PE MI-TR

Part no.:10.07.09.00083

External diameter D: 10 mm

Internal diameter d: 7 mm

Length max.: 50 m

Material hose: PE

Bending radius min.: 60 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -30 ... 70 °C



#### VSL 10-7 PU MI-TR

Part no.:10.07.09.00084

External diameter D: 10 mm

Internal diameter d: 7 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 60 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -40 ... 85 °C

### Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | [schmalz@schmalz.com.tr](mailto:schmalz@schmalz.com.tr)