

Plug union, straight

STVI-GE G1/4-IG 10

Part no...:10.08.02.00260

<https://www.schmalz.com/10.08.02.00260>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STVI-GE G1/4-IG 10

Push-in Fitting, straight



Thread G1: G1/4"-F

Hose diameter: 10 mm


Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 16.5 mm

Length L: 37 mm

Design Data



Attribute	Value
D	16.50 mm
d	10 mm
G1	G1/4"-F
dn	8 mm
L	37 mm
L2	17.50 mm
LG1	12 mm
SW1	17 mm

Technical Data

Attribute	Value
Hose type	Hose D = 10 d = 7
Hose type	10-7
Material	Brass
Pressure range (operating pressure)	0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Weight	34 g
Product family	STV

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | schmalz@schmalz.com.tr

Plug union, straight

STVI-GE G1/4-IG 10

Part no.:10.08.02.00260

<https://www.schmalz.com/10.08.02.00260>

Accessories



VSL 10-7 PE MI-TR

Part no.:10.07.09.00083

External diameter D: 10 mm

Internal diameter d: 7 mm

Length max.: 50 m

Material hose: PE

Bending radius min.: 60 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -30 ... 70 °C



VSL 10-7 PU MI-TR

Part no.:10.07.09.00084

External diameter D: 10 mm

Internal diameter d: 7 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 60 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -40 ... 85 °C

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | schmalz@schmalz.com.tr