

Flat suction cup (oval)

SGO 24x8 NBR-55 N022

Part no...:10.01.05.00151

<https://www.schmalz.com/10.01.05.00151>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Oval) > SGO 24x8 NBR-55 N022

Flat suction cup (oval) for narrow or curved workpieces




Dimensions (LxB): 24 x 8

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
Bmax(S)	9 mm
Bs	7.60 mm
d	5.50 mm
d1	7 mm
dn	1.50 mm
Dk	11.50 mm
Lmax(S)	24.50 mm
Ls	23.60 mm
H	12 mm
H2	3 mm
H3	5.50 mm
Z (Stroke)	1 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	8 N
Dimensions (LxB)	24 x 8
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Weight	2.50 g

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | schmalz@schmalz.com.tr

Flat suction cup (oval)

SGO 24x8 NBR-55 N022

Part no...:10.01.05.00151

<https://www.schmalz.com/10.01.05.00151>

Product family

SGO

Accessories



SA-NIP N022 G1/8-AG DN350

Part no...:10.01.05.00124


Thread G1: G1/8"-M

Length L1: 18.5 mm

Fitting length: 5 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



SA-NIP N022 G1/8-IG DN350

Part no...:10.01.05.00123

Thread G1: G1/8"-F

Length L1: 18.5 mm

Fitting length: 13 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | schmalz@schmalz.com.tr