

Flat suction cup (oval)

SGON 60x20 NBR-55 G1/4-IG

Part no.:10.01.05.00095

<https://www.schmalz.com/10.01.05.00095>

Home > Flat Suction Cups SGON > SGON 60x20 NBR-55 G1/4-IG

Flat suction cup (oval) for long and also curved workpieces



Dimensions (LxB): 60 x 20


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Connection: G1/4"-F

Design Data



Attribute	Value
Bmax(S)	22 mm
Bs	20 mm
dn	3.50 mm
G1	G1/4"-F
H	36 mm
LG1	12 mm
Lmax(S)	61 mm
Ls	60 mm
SW1	17 mm
Z (Stroke)	2.50 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 M3.

Technical Data

Attribute	Value
Suction force (-600mbar)	50.10 N
Volume	3.61 cm ³
Curve radius (min) (convex)	20 mm
Hose diameter (rec.) d	6 mm
Dimensions (LxB)	60 x 20
Number of folds	0
Suction cup material	Nitrile rubber NBR

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0123 | schmalz@schmalz.com.tr

Flat suction cup (oval)

SGON 60x20 NBR-55 G1/4-IG

Part no.:10.01.05.00095

<https://www.schmalz.com/10.01.05.00095>

Material hardness [Shore A]	55 Shore A
Weight	18.50 g
Product family	SGON

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N023 G1/4-IG DN350

Part no.:10.01.05.00121

Thread G1: G1/4"-F
Length L1: 25 mm
Fitting length: 15 mm
Nominal diameter dn: 3.5 mm
Material: Aluminum



ZOKL 15-18

Part no.:10.07.10.00033

Clamping range: 15.0 ... 18.0 mm
Material: Galvanized steel

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0123 | schmalz@schmalz.com.tr

Flat suction cup (oval)

SGON 60x20 NBR-55 G1/4-IG

Part no...:10.01.05.00095

<https://www.schmalz.com/10.01.05.00095>



SGO 60x20 NBR-55 N023

Part no...:10.01.05.00154

Dimensions (LxB): 60 x 20

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A



ZOKL 15-18

Part no...:10.07.10.00033

Clamping range: 15.0 ... 18.0 mm

Material: Galvanized steel

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 310 0113 | schmalz@schmalz.com.tr