

Sealing profile (meter)


DI-PROF 25x20 MOS EPDM-20

Part no...:10.07.04.00007

<https://www.schmalz.com/10.07.04.00007>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Sealing Profiles > Sealing Profiles DI-PROF > DI-PROF 25x20 MOS EPDM-20

Sealing section for construction of specific gripper solutions



Width B: 25 mm


Height H: 20 mm

Material type: Foam rubber

Sealing material: EPDM

Material hardness [Shore A]: 20 Shore A

Design Data



Attribute

Value

B

25 mm

H

20 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 E3

Technical Data

Attribute	Value
Sealing material	EPDM
Recommended slot width x slot depth [mm]	26 x 10
Weight	150 g
Material hardness [Shore A]	20 Shore A
Product family	DI-PROF

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | schmalz@schmalz.com.tr



Sealing profile (meter)

DI-PROF 25x20 MOS EPDM-20

Part no...:10.07.04.00007

<https://www.schmalz.com/10.07.04.00007>

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | schmalz@schmalz.com.tr