

Flat suction cup (round)

SG 25 NBR-55 N027

Part no...:10.01.01.00196

<https://www.schmalz.com/10.01.01.00196>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Different Industries > SG 25 NBR-55 N027

Flat suction cup (round)



Size: 25

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Height H: 31 mm

Design Data



Attribute	Value
d	8 mm
Dk	12 mm
Dmax(S)	27 mm
Ds	25 mm
H	31 mm
H2	18 mm
Z (Stroke)	5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Number of folds	0
Size	25
Suction cup material	Nitrile rubber NBR
Suction force (-600mbar)	24 N
Material hardness [Shore A]	55 Shore A
Product family	SG

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | schmalz@schmalz.com.tr


Flat suction cup (round)

SG 25 NBR-55 N027

Part no...:10.01.01.00196

<https://www.schmalz.com/10.01.01.00196>

Accessories



SA-NIP N027 G1/8-AG DN350

Part no...:10.01.01.00320

Thread G1: G1/8"-M

Fitting length: 3 mm

Material: Aluminum

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | schmalz@schmalz.com.tr