

Bellows suction cups (round)

SPB2f 20 SI-55 G1/8-IG

Part no...:10.01.06.04313

<https://www.schmalz.com/10.01.06.04313>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for the Packaging Industry > Bellows Suction Cups SPB2f (2.5 Folds) > SPB2f 20 SI-55 G1/8-IG

Bellows suction cup (round) for very uneven workpieces



Size: 20


Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Thread G1: G1/8"-F

Number of folds: 2.5

Design Data



Attribute	Value
d2	6 mm
dn	4.10 mm
Dmax(S)	22.50 mm
Ds	20 mm
G1	G1/8"-F
H	37.40 mm
LG1	8 mm
SW1	14 mm
Z (Stroke)	9.10 mm

Technical Data

Attribute	Value
Suction force at -200 mbar	0.60 N
Suction force at -400 mbar	1.10 N
Suction force (-600mbar)	1.70 N
Volume	1.86 cm ³
Size	20
Number of folds	2.50
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | schmalz@schmalz.com.tr

Bellows suction cups (round)

SPB2f 20 SI-55 G1/8-IG

Part no.:10.01.06.04313

<https://www.schmalz.com/10.01.06.04313>

Weight	7.30 g
Product family	SPB2f

Spare parts



SC 040 G1/8-IG

Part no.:10.01.06.02482

Connection geometry: 040

Connection: G1/8"-F

Length L1: 20.7 mm

Fitting length: 14 mm

Nominal diameter dn: 4.1 mm



SPB2f 20 SI-55 SC040

Part no.:10.01.06.04225

Size: 20

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Number of folds: 2.5

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | schmalz@schmalz.com.tr