

Ball valve

KVD 20 3/2

Part no...:10.05.08.00004

<https://www.schmalz.com/10.05.08.00004>


Home > Three-Way Ball Valves KVD > KVD 20 3/2

Three-way ball valve for manual switching of vacuum and compressed air



Nominal size: 20 mm
Function: 3/2-way valve
Thread G1: G3/4"-F
Pressure range (operating pressure): -0.95 ... 16.00 bar

Design Data



Attribute	Value
B	70 mm
D1	47 mm
G1	G3/4"-F
H	107 mm
L	92 mm
L2	145 mm
LG1	23 mm
SW1	34 mm

Technical Data

Attribute	Value
Nominal size	20 mm
Nominal flow rate	45 m³/h
Nominal flow rate	750 l/min
Weight	1.26 kg
Product family	KVD

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0121 | schmalz@schmalz.com.tr