

Plug union, elbow

STV-W G1/4-AG 10

Part no.:10.08.03.00235

<https://www.schmalz.com/10.08.03.00235>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STV-W G1/4-AG 10

Push-in Fitting, swivelling elbow



Thread G1: G1/4"-M


Hose diameter: 10 mm

Material: Plastics

Operating temperature: 0 ... 60 °C

Length L: 27 mm

Design Data



Attribute	Value
d	10 mm
G1	G1/4"-M
dn	7 mm
D1	19 mm
H	16.50 mm
H1	26.10 mm
L	27 mm
L1	34.50 mm
LG1	6 mm
SW1	16 mm

Technical Data

Attribute	Value
Hose type	Hose D = 10 d = 7
Hose type	10-7
Material	Plastics
Pressure range (operating pressure)	0.95 ... 10.00 bar
Operating temperature	0 ... 60 °C
Weight	28.70 g
Product family	STV

Contact Schmalz

Schmalz Inc. | 5850 Oak Forest Drive, Raleigh, NC 27616, United States | +1 (919) 713-0880 | schmalz.us@schmalz.com



Plug union, elbow

STV-W G1/4-AG 10

Part no...:10.08.03.00235

<https://www.schmalz.com/10.08.03.00235>

Contact Schmalz

Schmalz Inc. | 5850 Oak Forest Drive, Raleigh, NC 27616, United States | +1 (919) 713-0880 | schmalz.us@schmalz.com