

Plug union, T

STV-T G1/8-AG 8

Part no.: 10.09.02.00041

<https://www.schmalz.com/10.09.02.00041>

Home > Screw in Push Fittings > STV-T G1/8-AG 8

Push-in Fitting, T



Thread G1: G1/8"-M


Hose diameter: 8 mm

Material: Brass

Operating temperature: °C

Length L: 48.7 mm

Design Data



Attribute	Value
d	8 mm
G1	G1/8"-M
dn	5.50 mm
D1	14.10 mm
H	15 mm
H1	22 mm
L	48.70 mm
LG1	5.50 mm
SW1	13 mm

Technical Data

Attribute	Value
Hose type	Hose D = 8 d = 6
Hose type	8-6
Material	Brass
Pressure range (operating pressure)	bar
Operating temperature	°C
Weight	51.60 g
Product family	STV

Contact Schmalz

Schmalz Inc. | 5850 Oak Forest Drive, Raleigh, NC 27616, United States | +1 (919) 713-0880 | schmalz.us@schmalz.com

Plug union, T

STV-T G1/8-AG 8

Part no.:10.09.02.00041

<https://www.schmalz.com/10.09.02.00041>

Accessories



VSL 8-6 PE BL

Part no.:10.07.09.00015

External diameter D: 8 mm

Internal diameter d: 6 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 8-6 PU MI-TR

Part no.:10.07.09.00003

External diameter D: 8 mm

Internal diameter d: 6 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 45 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -35 ... 60 °C

Contact Schmalz

Schmalz Inc. | 5850 Oak Forest Drive, Raleigh, NC 27616, United States | +1 (919) 713-0880 | schmalz.us@schmalz.com