

Holder tooling suction Cup

HT-SG A5 I 10 46 RA AB

Part no.:10.07.06.00486

<https://www.schmalz.com/10.07.06.00486>

Home > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Holder System for Tooling HT > Holders for Suction Cups HT-SG I > HT-SG A5 I 10 46 RA AB

Holder for suction cup



Connection 1: Ball head 32 mm

Shape: integrated nozzle


Suction cup connection: Rectangular adapter

Vacuum connection: G1/8\"-F

Connection: Rectangular adapter

Add. function: Active blowing off

Design Data



Attribute	Value
B	46 mm
B1	77 mm
B2	31 mm
B3	32 mm
D	32 mm
G3	G1/8\"-F
G4	G1/8\"-F
H	24.50 mm
H1	47.70 mm
H2	4.80 mm
L	45.50 mm
L1	82 mm
L2	67 mm
L3	15 mm

Technical Data

Attribute	Value
Weight	180.60 g
Product family	HT-SG-I

Contact Schmalz

Schmalz Inc. | 5850 Oak Forest Drive, Raleigh, NC 27616, United States | +1 (919) 713-0880 | schmalz.us@schmalz.com

Holder tooling suction Cup

HT-SG A5 I 10 46 RA AB

Part no.:10.07.06.00486

<https://www.schmalz.com/10.07.06.00486>

Accessories



STV-GE G1/8-AG 6

Part no.:10.08.02.00204

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 11.4 mm

Length L: 16.4 mm



STV-W G1/8-AG 6

Part no.:10.08.02.00288

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Plastics

Operating temperature: °C

Length L: 20.8 mm

Contact Schmalz

Schmalz Inc. | 5850 Oak Forest Drive, Raleigh, NC 27616, United States | +1 (919) 713-0880 | schmalz.us@schmalz.com