

Floating suction cup

SBS 20 HF M5-IG AL

Part no...:10.01.01.12650

<https://www.schmalz.com/10.01.01.12650>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Floating Suction Cups > Floating Suction Cups SBS > SBS 20 HF M5-IG AL

Floating suction cup for handling sensitive workpieces




Diameter: 20 mm

Shape: High Flow

Compressed-air connection: M5-F

Material: Aluminum

Design Data



Attribute	Value
B	22.20 mm
D	20 mm
G1	M5-F
G2	M3-F
G3	M5-F
H	17 mm
H1	17.50 mm
LG1	5 mm
LG2	6 mm
LG3	6 mm
X1	15 mm

Technical Data

Attribute	Value
Holding force	3 N
Air consumption	8.40 m³/h
Air consumption	140 l/min
Pressure range (operating pressure)	1.0 ... 6.0 bar
Weight	12 g
Product family	SBS

Contact Schmalz

Schmalz Inc. | 5850 Oak Forest Drive, Raleigh, NC 27616, United States | +1 (919) 713-0880 | schmalz.us@schmalz.com

Floating suction cup

SBS 20 HF M5-IG AL

Part no...:10.01.01.12650

<https://www.schmalz.com/10.01.01.12650>

Note: Air consumption: The values provided are based on an operating pressure of 5 bar, measured on a suction-tight workpiece. The actual values may differ depending on the properties of the workpiece.

Spare parts



REIB-FL SBS HT1-60

Part no...:10.01.01.12585

Construction use: Floating suction cup

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

External diameter D: 2.5 mm