

## Bellows suction cups (round)

FSG 9 HT1-60 G1/8-IG

Part no.:10.01.06.00978

<https://www.schmalz.com/10.01.06.00978>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSG (2.5 Folds) > FSG 9 HT1-60 G1/8-IG

### Bellows suction cup (round) for very uneven workpieces



Size: 9

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A


Nipple material: Aluminum

Connection: G1/8"-F

Number of folds: 2.5

Vacuum connection: G1/8"-F

### Design Data



Attribute	Value
d2	4.10 mm
dn	3.50 mm
Dmax(S)	9.50 mm
Ds	9 mm
G1	G1/8"-F
H	27 mm
LG1	8.50 mm
SW1	14 mm
Z (Stroke)	3 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

### Technical Data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Size	9
Number of folds	2.50
Connection	G1/8-IG
Curve radius (min) (convex)	10 mm
Volume	0.15 cm <sup>3</sup>

### Contact Schmalz

Schmalz Inc. | 5850 Oak Forest Drive, Raleigh, NC 27616, United States | +1 (919) 713-0880 | [schmalz.us@schmalz.com](mailto:schmalz.us@schmalz.com)

## Bellows suction cups (round)

FSG 9 HT1-60 G1/8-IG

Part no.:10.01.06.00978

<https://www.schmalz.com/10.01.06.00978>

Suction force (-600mbar)	0.79 N
Pull-off force	2.30 N
Hose diameter (rec.) d	4 mm
Weight	4.90 g
Product family	FSG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

### Accessories



#### SPI 9 PEEK

Part no.:10.01.06.03280

Size: 9

Material: Polyetheretherketon

### Spare parts



#### SA-NIP N016 G1/8-IG DN350

Part no.:10.01.06.05731

Nipple family: N 016

Thread G1: G1/8"-F

Length L1: 18.5 mm

Fitting length: 12 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum

### Contact Schmalz

Schmalz Inc. | 5850 Oak Forest Drive, Raleigh, NC 27616, United States | +1 (919) 713-0880 | [schmalz.us@schmalz.com](mailto:schmalz.us@schmalz.com)

## Bellows suction cups (round)

FSG 9 HT1-60 G1/8-IG

Part no...:10.01.06.00978

<https://www.schmalz.com/10.01.06.00978>



### FG 9 HT1-60 N016

Part no...:10.01.06.00878

Size: 9

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Number of folds: 2.5

### Contact Schmalz

Schmalz Inc. | 5850 Oak Forest Drive, Raleigh, NC 27616, United States | +1 (919) 713-0880 | [schmalz.us@schmalz.com](mailto:schmalz.us@schmalz.com)