

Flat suction cup (round)

SGP 34 NK-40 N033

Part no.:10.01.01.10829

<https://www.schmalz.com/10.01.01.10829>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > SGP 34 NK-40 N033

Flat suction cup (round) for careful gripping of paper, plastic film, etc.




Size: 34

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 40 Shore A

Design Data



Attribute	Value
d	11.20 mm
Dk	15.20 mm
Dmax(S)	37.50 mm
Ds	34 mm
H	23 mm
H2	16.80 mm
Z (Stroke)	2.20 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	25 N
Volume	3.70 cm ³
Size	34
Nipple family	N 033
Number of folds	0
Suction cup material	Natural Rubber NK
Material hardness [Shore A]	40 Shore A

Contact Schmalz

Schmalz Inc. | 5850 Oak Forest Drive, Raleigh, NC 27616, United States | +1 (919) 713-0880 | schmalz.us@schmalz.com

Flat suction cup (round)

SGP 34 NK-40 N033

Part no.:10.01.01.10829

<https://www.schmalz.com/10.01.01.10829>

Weight	5.60 g
Product family	SGP

Accessories



SA-NIP N033 G1/4-AG DN550

Part no.:10.01.01.00818

Thread G1: G1/4"-M

Fitting length: 5 mm

Material: Aluminum



SA-NIP N033 G1/4-IG DN550

Part no.:10.01.01.00817

Thread G1: G1/4"-F

Fitting length: 15 mm

Material: Aluminum

Contact Schmalz

Schmalz Inc. | 5850 Oak Forest Drive, Raleigh, NC 27616, United States | +1 (919) 713-0880 | schmalz.us@schmalz.com