

Flat suction pad (round)

SFF 30 HT1-60 G1/4-AG

Part no.:10.01.01.14280

<https://www.schmalz.com/10.01.01.14280>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Suction Cups SFF / SFB1 > SFF 30 HT1-60 G1/4-AG

Flat suction cup (round) for dynamic handling of thin and flexible workpieces



Size: 30

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Number of folds: 0

Design Data



Attribute	Value
G1	G1/4"-M
Dmax(S)	31.50 mm
Ds	30 mm
dn	4 mm
LG1	10 mm
H	19.50 mm
SW1	17 mm
Z (Stroke)	2 mm

Technical Data

Attribute	Value
Size	30
Suction cup material	High temperature material HT1
Suction force (-600mbar)	26.90 N
Product family	SFF
Volume	1.70 cm ³
Number of folds	0
Material hardness [Shore A]	60 Shore A

Contact Schmalz

Schmalz Inc. | 5850 Oak Forest Drive, Raleigh, NC 27616, United States | +1 (919) 713-0880 | schmalz.us@schmalz.com


Flat suction pad (round)

SFF 30 HT1-60 G1/4-AG

Part no.:10.01.01.14280

<https://www.schmalz.com/10.01.01.14280>

Spare parts



SFF 30 HT1-60 SC040

Part no.:10.01.01.14054

Size: 30

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Number of folds: 0



SC 040 G1/4-AG

Part no.:10.01.06.03414

Connection geometry: 040

Vacuum connection: G1/4"-M

Fitting length: 6 mm

Nominal diameter dn: 4.1 mm

Contact Schmalz

Schmalz Inc. | 5850 Oak Forest Drive, Raleigh, NC 27616, United States | +1 (919) 713-0880 | schmalz.us@schmalz.com