

## Flat suction cup (oval)

### SGO 30x10 FPM-50 N022

Part no.:10.01.05.00848

<https://www.schmalz.com/10.01.05.00848>

Homepage > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Oval) > SGO 30x10

FPM-50 N022

## Flat suction cup (oval) for narrow or curved workpieces



Dimensions (LxW): 30 x 10 mm

Suction cup material:

Fluorocautchuc FPM

Material hardness: 50 °Sh

## Design Data



Attribute	Value
Bmax(S)	11.5 mm
Bs	9.4 mm
d	5.5 mm
d1	7 mm
dn	2.5 mm
Dk	11.5 mm
Lmax(S)	30.5 mm
Ls	29.4 mm
H	12 mm
H2	3 mm
H3	5.5 mm
Z (Stroke)	1.5 mm



## Flat suction cup (oval)

SGO 30x10 FPM-50 N022

Part no.:10.01.05.00848

<https://www.schmalz.com/10.01.05.00848>

### Technical Data

Attribute	Value
Dimensions (LxB)	30 x 10
Suction cup material	Fluorocaoutchuc FPM
Material hardness [Shore A]	50 Shore A
Weight	1.8 g
Number of folds	0
Product family	SGO

---

---