

Multi-Clamp suction plate

VC-M-SPV 160x160x30

Part no.:10.01.12.01853

<https://www.schmalz.com/10.01.12.01853>

Homepage > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Manual Work > Multi-Clamp

Suction Plates VC-M-SP / VC-M-SPV > VC-M-SPV 160x160x30

Multi-Clamp - Suction plate for operation with vacuum pump




Length L: 160 mm

Width B: 160 mm

Height H: 30 mm

Design Data



Attribute	Value
B	160 mm
H	30 mm
d	6 mm
L	160 mm

Technical Data

Attribute	Value
Weight	0.896 kg

Multi-Clamp suction plate

VC-M-SPV 160x160x30

Part no.:10.01.12.01853

<https://www.schmalz.com/10.01.12.01853>

Accessories



FU 5 3/2 -

Part no.10.01.12.02055

Foot-operated valve for control of compressed air and vacuum

Nominal size: 5 mm

Function: 3/2-way valve

Thread G1: G1/4"-F

with: None



VC-M-BV 265x170x209

Part no.10.01.12.02050

Turning and slewing device Base

Length L: 265 mm

Width B: 170 mm

Height H: 209 mm



VC-M-PU 4 110V-AC

Part no.10.01.12.02051

Multi-Clamp Vacuum pump

Current type: 1-phase AC 110V

Voltage: 110V - AC

Vacuum (max): -850 mbar

Suction rate: 4 m³/h

Nominal size: 9 mm

Multi-Clamp suction plate

VC-M-SPV 160x160x30

Part no.:10.01.12.01853

<https://www.schmalz.com/10.01.12.01853>



VC-M-PU 4 230V-AC

Part no.10.01.12.02040

Multi-Clamp Vacuum pump


Current type: 1-phase AC 230V

Voltage: 230V - AC

Vacuum (max): -850 mbar

Suction rate: 4 m³/h

Nominal size: 9 mm



ZUB VC-M-V

Part no.10.01.12.02054

Accessories

for: Multi-Clamp