

## Vacuum block


### VCBL-R 160x160x45 30/50 TV

Part no.:10.01.12.02670

<https://www.schmalz.com/10.01.12.02670>

Homepage > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Grid Table Systems > Vacuum block VCBL-R > VCBL-R 160x160x45 30/50 TV

## Vacuum block for grid tables



Dimensions (LxW): 160 x 160 mm


Height H: 45 mm

grid: 30x30 mm / 50x50 mm mm

for slot: 6,5x6,5 / 7,5x7,5 mm

with: Sensing valve

## Design Data



Attribute	Value
B	160 mm
H	45 mm
L	160 mm

## Technical Data

Attribute	Value
Grid	30/50
Weight	0.861 kg

## Vacuum block

VCBL-R 160x160x45 30/50 TV

Part no.:10.01.12.02670

<https://www.schmalz.com/10.01.12.02670>

### Spare Parts




#### TV D9 4.3

Part no.10.01.12.02514

Touch valve for deactivation of unused suction cups or vacuum blocks

External diameter D: 9 mm

Spring stroke Z: 4.3 mm



#### ERS VCBL-R Winkel


Part no.10.01.12.02691

Set of spare parts

for: Vacuum block VCBL-R

contains: adjustment-angle

and: Screws



#### ERS VCBL-R

Part no.10.01.12.02693

Set of spare parts


for: Vacuum block VCBL-R

## Vacuum block

VCBL-R 160x160x45 30/50 TV

Part no.:10.01.12.02670

<https://www.schmalz.com/10.01.12.02670>



### **ISDR 150x150x13.5 R 30/50**

Part no.10.01.15.00352

Sealing frame

Length L: 150 mm

Width B: 150 mm

Height H: 13.5 mm

Type: R 30/50