

Schmalz Suction Plate Balance

SSPB-117 117-125 NBR

Part no.:10.01.15.00719

<https://www.schmalz.com/10.01.15.00719>



Homepage > Vacuum Clamping Technology > Clamping Equipment for 3D Freeform Surfaces > Clamping Equipment for Manual Processing >


Basic Holding Fixture BHF > SSPB-117 117-125 NBR

Suction plate with ball support for flexible clamping and gripping systems



Diameter Ds: 117 mm
Operating altitude (range):
117.0 ... 125.0 mm
Material workpiece support: Elastodur
Sealing material: Perbunan
Diameter vacuum connection: 60 mm
Height H1: 137 mm

Design Data



Attribute	Value
D	60 mm
Ds	117 mm
EH (max)	125 mm
EH (min)	117 mm
H1	137 mm
Z (Stroke)	8 mm