

Flat suction cup (round)

PFYN 35 FPM-65 G1/8-AG

Part no.:10.01.01.00187

<https://www.schmalz.com/10.01.01.00187>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups PFYN > PFYN 35 FPM-65 G1/8-AG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 35

Suction cup material: Fluorocautchuc FPM


Material hardness [Shore A]: 65 Shore A

Material property: non-marking

Nipple material: Aluminum

Vacuum connection: G1/8"-M

Design Data



Attribute	Value
dn	2.40 mm
Dmax(S)	38 mm
Ds	35 mm
G1	G1/8"-M
H	19 mm
LG1	8 mm
SW1	14 mm
Z (Stroke)	3 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	44 N
Size	35
Suction cup material	Fluorocautchuc FPM
Material hardness [Shore A]	65 Shore A
Weight	13.30 g
Product family	PFYN
Number of folds	0

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (round)

PFYN 35 FPM-65 G1/8-AG

Part no.: 10.01.01.00187

<https://www.schmalz.com/10.01.01.00187>

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SU 30

Part no.: 10.01.01.12889

Size: 30

Clamping range: 27.0 ... 35.0 mm

Temperature resistance: 80 °C

Spare parts



SA-NIP N007 G1/8-AG DN240

Part no.: 10.01.01.03531

Nipple family: N 007

Thread G1: G1/8"-M

Length L1: 21 mm

Length L: 5 mm

Fitting length: 5 mm

Nominal diameter dn: 2.4 mm

Material: Aluminum

Spanner size SW2: 4 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (round)

PFYN 35 FPM-65 G1/8-AG

Part no...:10.01.01.00187

<https://www.schmalz.com/10.01.01.00187>



PFG 35 FPM-65 N007

Part no...:10.01.01.00075

Size: 35

Suction cup material: Fluorocaotchuc FPM

Material hardness [Shore A]: 65 Shore A

Material property: non-marking