

## Flat suction cup (round)

PFYN 60 FPM-65 G1/4-AG

Part no.:10.01.01.00190

<https://www.schmalz.com/10.01.01.00190>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups PFYN > PFYN 60 FPM-65 G1/4-AG

### Flat suction cup (round) for smooth or slightly rough surfaces



Size: 60

Suction cup material: Fluorocaotchuc FPM


Material hardness [Shore A]: 65 Shore A

Material property: non-marking

Nipple material: Aluminum

Vacuum connection: G1/4"-M

### Design Data



| Attribute  | Value   |
|------------|---------|
| dn         | 5.50 mm |
| Dmax(S)    | 64 mm   |
| Ds         | 60 mm   |
| G1         | G1/4"-M |
| H          | 23 mm   |
| LG1        | 10 mm   |
| SW1        | 17 mm   |
| Z (Stroke) | 4.70 mm |

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

### Technical Data

| Attribute                   | Value              |
|-----------------------------|--------------------|
| Suction force (-600mbar)    | 125 N              |
| Volume                      | 10 cm <sup>3</sup> |
| Curve radius (min) (convex) | 100 mm             |
| Hose diameter (rec.) d      | 6 mm               |
| Size                        | 60                 |
| Suction cup material        | Fluorocaotchuc FPM |
| Material hardness [Shore A] | 65 Shore A         |

### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)

## Flat suction cup (round)

PFYN 60 FPM-65 G1/4-AG

Part no.:10.01.01.00190

<https://www.schmalz.com/10.01.01.00190>

|                 |      |
|-----------------|------|
| Weight          | 41 g |
| Product family  | PFYN |
| Number of folds | 0    |

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

### Accessories



#### SU 60

Part no.:10.01.01.13585

Size: 60

Clamping range: 60.0 ... 70.0 mm

Temperature resistance: 80 °C

### Spare parts



#### SA-NIP N009 G1/4-AG

Part no.:10.01.01.10097

Thread G1: G1/4"-M

Length L1: 25 mm

Material: Aluminum

## Flat suction cup (round)

PFYN 60 FPM-65 G1/4-AG

Part no...:10.01.01.00190

<https://www.schmalz.com/10.01.01.00190>



**PFG 60 FPM-65 N009 M10x1.25-IG**

Part no...:10.01.01.00078

Size: 60

Suction cup material: Fluorocaotchuc FPM

Material hardness [Shore A]: 65 Shore A

Material property: non-marking

### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)