

Flat suction cup (round)

SG 6.3 NBR-55 N024

Part no...:10.01.01.00193

<https://www.schmalz.com/10.01.01.00193>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Different Industries > SG 6.3 NBR-55 N024

Flat suction cup (round)




Size: 6.3

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Height H: 12 mm

Design Data



Attribute	Value
d	2 mm
Dk	4 mm
Dmax(S)	7 mm
Ds	6.30 mm
H	12 mm
H2	8.50 mm
Z (Stroke)	1.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Number of folds	0
Size	6.30
Suction cup material	Nitrile rubber NBR
Suction force (-600mbar)	1.50 N
Material hardness [Shore A]	55 Shore A
Product family	SG

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (round)

SG 6.3 NBR-55 N024

Part no.:10.01.01.00193

<https://www.schmalz.com/10.01.01.00193>

Accessories



SA-NIP N024 M5-AG DN100

Part no.:10.01.01.00317

Thread G1: M5-M

Fitting length: 3 mm

Material: Aluminum

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de