

Flat suction cup (round)

SG 45 SI-60 N031

Part no.:10.01.01.00220

<https://www.schmalz.com/10.01.01.00220>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Different Industries > SG 45 SI-60 N031

Flat suction cup (round)




Size: 45

Suction cup material: Silicone SI

Material hardness [Shore A]: 60 Shore A

Height H: 26 mm

Design Data



Attribute	Value
d	9 mm
Dk	20 mm
Dmax(S)	50 mm
Ds	44.20 mm
H	26 mm
H2	13.40 mm
Z (Stroke)	5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Number of folds	0
Size	45
Suction cup material	Silicone SI
Suction force (-600mbar)	50 N
Material hardness [Shore A]	60 Shore A
Product family	SG

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (round)

SG 45 SI-60 N031

Part no.:10.01.01.00220

<https://www.schmalz.com/10.01.01.00220>

Accessories



SA-NIP N031 G1/4-AG DN550

Part no.:10.01.01.00327

Thread G1: G1/4"-M

Fitting length: 5 mm

Material: Aluminum



SA-NIP N031 G1/4-IG DN550

Part no.:10.01.01.00328

Thread G1: G1/4"-F

Fitting length: 21 mm

Material: Aluminum

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de