

Suction plate (round)

SPL-HT 190 FPM-F-65

Part no.:10.01.01.00834

<https://www.schmalz.com/10.01.01.00834>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for High-Temperature Applications > SPL-HT 190 FPM-F-65

Suction plate for high-temperature applications




Size: 190

Suction cup material: Fluorocautchuc FPM-F

Material hardness [Shore A]: 65 Shore A

Working temperature max.: 350 °C

Design Data



Attribute	Value
d	40 mm
Dmax(S)	209 mm
Ds	190 mm
H	17 mm
Z (Stroke)	8 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	1050 N
Curve radius (min) (convex)	350 mm
Size	190
Working temperature max.	350 °C
Suction cup material	Fluorocautchuc FPM-F
Weight	256 g
Product family	SPL-HT

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Suction plate (round)

SPL-HT 190 FPM-F-65

Part no.:10.01.01.00834

<https://www.schmalz.com/10.01.01.00834>
