

Sealing profile (meter)

DI-PROF 9x9.7 2K-MOS CR-20/60

Part no.:10.01.01.10527

<https://www.schmalz.com/10.01.01.10527>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Sealing Profiles > Sealing Profiles DI-PROF > DI-PROF 9x9.7 2K-MOS CR-20/60

Sealing section for construction of specific gripper solutions



Width B: 9 mm


Height H: 9.7 mm

Material type: 2 Comp. foam rubber

Sealing material: Chloroprene CR

Material hardness [Shore A]: 20 Shore A

Design Data



Attribute	Value
B	9 mm
B1	14.50 mm
B2	3.90 mm
B3	5.90 mm
B4	9.60 mm
H	9.70 mm
H1	26.50 mm
H2	2 mm
H3	4.70 mm
H4	10 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 E3

Technical Data

Attribute	Value
Sealing material	Chloroprene CR
Weight	310 g
Material hardness [Shore A]	20 Shore A
Product family	DI-PROF

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de