

Flat suction cup (round)

PFYN 80 HT1-60 G1/4-IG

Part no.:10.01.01.11157

<https://www.schmalz.com/10.01.01.11157>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups PFYN > PFYN 80 HT1-60 G1/4-IG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 80

Suction cup material: High temperature material HT1


Material hardness [Shore A]: 60 Shore A

Material property: non-marking

Nipple material: Aluminum

Vacuum connection: G1/4"-F

Design Data



Attribute	Value
dn	5.50 mm
Dmax(S)	86 mm
Ds	80 mm
G1	G1/4"-F
H	41 mm
LG1	11 mm
SW1	17 mm
Z (Stroke)	6 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	260 N
Volume	25 cm ³
Curve radius (min) (convex)	150 mm
Hose diameter (rec.) d	6 mm
Size	80
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (round)

PFYN 80 HT1-60 G1/4-IG

Part no.:10.01.01.11157

<https://www.schmalz.com/10.01.01.11157>

Weight 65.20 g

Product family PFYN

Number of folds 0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SU 80


Part no.:10.01.01.12839

Size: 80

Clamping range: 80.0 ... 100.0 mm

Temperature resistance: 80 °C

Spare parts



SA-NIP N009 G1/4-IG

Part no.:10.01.01.10096

Thread G1: G1/4"-F

Length L1: 33 mm

Material: Aluminum

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (round)

PFYN 80 HT1-60 G1/4-IG

Part no...:10.01.01.11157

<https://www.schmalz.com/10.01.01.11157>



PFG 80 HT1-60 N009 M10x1.25-IG

Part no...:10.01.01.11170

Size: 80

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Material property: non-marking