

Edge gripper suction cup (oval)

SAOK 70x25 NBR-60 G1/4-AG

Part no.:10.01.01.12458

<https://www.schmalz.com/10.01.01.12458>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Edge Gripper Suction Cups SAOK (Oval) > SAOK 70x25 NBR-60 G1/4-AG

Edge gripper suction cup (oval) for dynamic handling of structured surfaces



Dimensions (LxB): 70 x 25


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Connection: G1/4-AG

Design Data



Attribute	Value
Bs	22.60 mm
dn	5 mm
G1	G1/4"-M
H	27.50 mm
LG1	8 mm
Lmax(S)	71 mm
Ls	67.20 mm
SW1	17 mm
Z (Stroke)	12.80 mm

Technical Data

Attribute	Value
Pull-off force	81 N
Pull-off force oily surface	60 N
Lateral force	46 N
Lateral force (oily surface)	20 N
Hose diameter (rec.) d	6 mm
Dimensions (LxB)	70 x 25
Workpiece angle (min)	80 °
Suction cup material	Nitrile rubber NBR

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Edge gripper suction cup (oval)

SAOK 70x25 NBR-60 G1/4-AG

Part no...:10.01.01.12458

<https://www.schmalz.com/10.01.01.12458>

Weight	27.30 g
Number of folds	0
Product family	SAOK

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de