

## Suction cup cover

SU 80

Part no.:10.01.01.12839

<https://www.schmalz.com/10.01.01.12839>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Accessories Vacuum Suction Cups > Suction Cup Covers SU > SU 80

### Cover for suction cup



Size: 80

Clamping range: 80.0 ... 100.0 mm

Temperature resistance: 80 °C

### Design Data



| Attribute | Value |
|-----------|-------|
| d         | 5 mm  |
| D         | 88 mm |
| D2        | 30 mm |

### Technical Data

| Attribute      | Value             |
|----------------|-------------------|
| Size           | 80                |
| Clamping range | 80.0 ... 100.0 mm |
| Weight         | 1.70 g            |
| Product family | SU                |

Note: In vertical applications with a suction plate or cup, the lateral force sinks by up to 70%. The vacuum generator must be able to provide 10% more suction power

### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)