

Flat suction cup (oval)

SAOF 60x23 HT2-65 G3/8-IG

Part no.:10.01.05.00741

<https://www.schmalz.com/10.01.05.00741>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Flat Suction Cups SAOF HT2 (Oval) > SAOF 60x23 HT2-65 G3/8-IG

Flat suction cup (oval) for very dynamic handling



Dimensions (LxB): 60 x 23

Suction cup material: High temperature material HT2

Material hardness [Shore A]: 65 Shore A

Nipple material: Nickel plated

Connection: G3/8-IG

Design Data



Attribute	Value
Bmax(S)	25 mm
Bs	21.60 mm
dn	6 mm
G1	G3/8"-F
H	26 mm
LG1	8 mm
Lmax(S)	64 mm
Ls	60.60 mm
SW1	22 mm
Z (Stroke)	3 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	57 N
Lateral force	36 N
Volume	3 cm ³
Curve radius (min) (convex)	20 mm
Hose diameter (rec.) d	4 mm
Dimensions (LxB)	60 x 23
Connection	G3/8"-F
Number of folds	0

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (oval)

SAOF 60x23 HT2-65 G3/8-IG

Part no.:10.01.05.00741

<https://www.schmalz.com/10.01.05.00741>

Suction cup material	High temperature material HT2
Material hardness [Shore A]	65 Shore A
Temperature resistance	200 °C
Weight	44.70 g
Product family	SAOF