

Bellows suction cup (round)

FGB 25 SI-55 N049

Part no.:10.01.06.00108

<https://www.schmalz.com/10.01.06.00108>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > FGB 25 SI-55 N049

Bellows suction cup (round) for very uneven workpieces




Size: 25

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Number of folds: 3.5

Design Data



Attribute	Value
d	5 mm
d2	10 mm
D1	25 mm
Dk	10 mm
Dmax(S)	26.50 mm
Ds	23 mm
H	43 mm
H2	9 mm
Z (Stroke)	22 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Number of folds	3.50
Size	25
Suction cup material	Silicone SI
Suction force (-600mbar)	4.50 N
Pull-off force	20 N
Volume	7.07 cm ³
Curve radius (min) (convex)	25 mm
Weight	5.50 g

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de



Bellows suction cup (round)

FGB 25 SI-55 N049

Part no...:10.01.06.00108

<https://www.schmalz.com/10.01.06.00108>

Product family

FGB

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Page 2 from 2