

Bellows suction cups (round)

FSGPL 120 NBR-55 G1/2-IG DR

Part no.:10.01.06.02993

<https://www.schmalz.com/10.01.06.02993>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups with Sealing Ring > FSGPL 120 NBR-55 G1/2-IG DR

Bellows suction cup (round) for large, heavy and uneven workpieces



Size: 120


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Nipple material: Steel

Number of folds: 1.5

Design Data



Attribute	Value
d2	79.30 mm
d3	69.40 mm
D1	127.80 mm
Dmax(S)	135 mm
Ds	96 mm
G1	G1/2"-F
H	51 mm
H4	8 mm
LG1	8 mm
Z (Stroke)	35.70 mm

Technical Data

Attribute	Value
Volume	290.68 cm ³
Curve radius (min) (convex)	150 mm
Hose diameter (rec.) d	12 mm
Size	120
Number of folds	1.50
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Weight	354 g

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de



Bellows suction cups (round)

FSGPL 120 NBR-55 G1/2-IG DR

Part no...:10.01.06.02993

<https://www.schmalz.com/10.01.06.02993>

Product family

FSGPL

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de