

Adapter plate


ISAP-R 175x175x7 30/50

Part no...:10.01.15.00184

<https://www.schmalz.com/10.01.15.00184>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Narrow Workpieces > Adapter-Plates
ISAP-R > ISAP-R 175x175x7 30/50

Adapter-Plate for grid tables



Dimensions (LxB): 175x175

Length L: 175 mm


Width B: 175 mm

Height H: 7 mm

Grid: 30/50

Recommended slot width x slot depth [mm]: 5x5 / 7x7

Design Data



Attribute

Value

B 175 mm

H 7 mm

L 175 mm

Accessories

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Adapter plate

ISAP-R 175x175x7 30/50

Part no...:10.01.15.00184

<https://www.schmalz.com/10.01.15.00184>



ISCUP Cup 1 80x80x30

Part no...:10.01.15.00003

Dimensions (LxB): 80 x 80

Length L: 80 mm

Width B: 80 mm

Height H: 30 mm



ISCUP Cup 2 80x40x30

Part no...:10.01.15.00004

Dimensions (LxB): 80 x 40

Length L: 80 mm

Width B: 40 mm

Height H: 30 mm



ISCUP Cup 3 80x28x30

Part no...:10.01.15.00005

Dimensions (LxB): 80 x 28

Length L: 80 mm

Width B: 28 mm

Height H: 30 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Adapter plate

ISAP-R 175x175x7 30/50

Part no.:10.01.15.00184

<https://www.schmalz.com/10.01.15.00184>



ISMB 80x80x8

Part no.:10.01.15.00188

Dimensions (LxB): 80x80

Basic area: 80 x 80 mm

Length L: 80 mm

Width B: 80 mm

Height H: 8 mm



ISMST 19-7 4ISMST

Part no.:10.01.14.00847

External diameter D: 7 mm

Height H: 11.5 mm

Spare parts



ISMST 19-7 4ISMST

Part no.:10.01.14.00847

External diameter D: 7 mm

Height H: 11.5 mm

Contact Schmalz


J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Adapter plate

ISAP-R 175x175x7 30/50

Part no...:10.01.15.00184

<https://www.schmalz.com/10.01.15.00184>



ISDR 167x167x9.3 NBR-55

Part no...:10.01.15.00182

Width B: 167 mm

Height H: 9.3 mm

Length L: 167 mm

Suction cup material: Nitrile rubber NBR-55