

Glass-Cup

ISCUP-G 80x80x30 Cup 1

Part no...:10.01.15.00392

<https://www.schmalz.com/10.01.15.00392>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Innospann Clamping Equipment ISCUP/ISMB/ISQB > ISCUP-G 80x80x30 Cup 1

Suction Glas-cup for Innospann



Dimensions (LxB): 80 x 80

Length L: 80 mm

Width B: 80 mm

Height H: 30 mm

Design Data



Attribute	Value
B	80 mm
H	30 mm
L	80 mm

Technical Data

Attribute	Value
Weight	0.17 kg

Spare parts

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Glass-Cup

ISCUP-G 80x80x30 Cup 1

Part no.:10.01.15.00392

<https://www.schmalz.com/10.01.15.00392>



DI-PROF 4x10 MOS EPDM HR

Part no.:10.01.15.00062

Width B: 4 mm

Height H: 10 mm

Sealing material: EPDM

Material type: Foam rubber

Form: half-round



ISDR 81x81x12 Cup 1 NBR-50

Part no.:10.01.15.00158

Length L: 81 mm

Width B: 81 mm

Height H: 12 mm