

Friction plate


ISRPL 86x86x8.7 NBR-55 d5

Part no...:10.01.15.00402

<https://www.schmalz.com/10.01.15.00402>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Accessories and Spare Parts > ISRPL 86x86x8.7 NBR-55 d5

Friction plate



Width B: 86 mm

Internal diameter d: 5 mm


Height H: 8.7 mm

Length L: 86 mm

Suction cup material: Nitrile rubber NBR-55

Type: CUP 100

Design Data



Attribute	Value
B	86 mm
d	5 mm
H	8.70 mm
L	86 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de