

Suction Cup Balance SSCB

SSCB-78 93.5-107.5 ZP 60 SAB-NBR

Part no.:10.01.15.00572

<https://www.schmalz.com/10.01.15.00572>

Home > Vacuum Clamping Technology > Clamping Equipment for 3D Freeform Surfaces > Clamping and Gripping Equipment for Automated Processing > Suction Cup Balance SSCB > SSCB-78 93.5-107.5 ZP 60 SAB-NBR

Vacuum Clamping System for automated 3D-fixation



Pitch diameter D mk: 78 mm

Function Suction cup: Centrally fixed pins

Suct. cups: Bellows suct. cup SAB

Connection: Ø60mm


Material: NBR

Material hardness [Shore A]: 60 Shore A

Material: NBR

Height H1: 117.3 mm

Design Data



Attribute	Value
D	60 mm
D1	116.40 mm
Dmk	78 mm
H1	117.30 mm
EH (min)	93.50 mm
EH (max)	107.50 mm
Zs	14 mm
Z (Stroke)	22 mm

Technical Data

Attribute	Value
Size	60
Weight	1300 g
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60 Shore A

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Suction Cup Balance SSCB

SSCB-78 93.5-107.5 ZP 60 SAB-NBR

Part no.:10.01.15.00572

<https://www.schmalz.com/10.01.15.00572>

Spare parts



SABT-C 60 NBR-60 M10-AG

Part no.:10.01.06.01878

Size: 60

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Vacuum connection: M10-M

Number of folds: 1.5

Height H: 39 mm



KAPP 7x10.5 SSCB

Part no.:10.01.15.00918

External diameter D: 7 mm

Length L: 10.5 mm

Construction use: Suction-Cup Balance

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de