

Magnetic gripper

SGM 70 G1/4-IG

Part no.:10.01.17.00165

<https://www.schmalz.com/10.01.17.00165>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Magnetic Grippers > Magnetic Grippers SGM > SGM 70 G1/4-IG

Magnetic gripper for handling metal sheets with holes




Size: 70

Socket: G1/4"-F

Holding force max. friction ring: 290 N

Pressure range (operating pressure): 3.5 ... 6.0 bar

Design Data



Attribute	Value
B	68.75 mm
D	68 mm
d	51 mm
G1	G1/4"-F
G2	G1/8"-F
G4	M5-F
H	80.20 mm
LG1	11 mm
LG2	6 mm
LG4	8 mm
X1	58 mm
Y1	15 mm

Technical Data

Attribute	Value
Holding force max. friction ring	290 N
Remaining force	0.30 N
Pressure range (operating pressure)	3.5 ... 6.0 bar
Installation position	BEL
Control valve	Bistable
Operating temperature	5 ... 70 °C

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Magnetic gripper

SGM 70 G1/4-IG

Part no.:10.01.17.00165

<https://www.schmalz.com/10.01.17.00165>

Weight	715 g
Product family	SGM

Note: Holding force: The value given is a statistical value with no safety factor; based on a plate with a thickness of 2 mm. For system configurations with magnetic grippers SGM, a safety factor of $S = 3$ must be applied

Accessories



HTS-A2 SGM 50/70 OP

Part no.:10.01.17.00578

Connection 1: Bolt with slot $\varnothing 19\text{mm}$

Construction use: Magnetic gripper

Size: 50/70



HTS-A2 D SGM 50/70 OP

Part no.:10.01.17.00587

Connection 1: Bolt with slot $\varnothing 19\text{mm}$

Construction use: Magnetic gripper

Size: 50/70

Shape: Double block

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Magnetic gripper

SGM 70 G1/4-IG

Part no...:10.01.17.00165

<https://www.schmalz.com/10.01.17.00165>



HTS-A3 SGM 50/70 OP

Part no...:10.01.17.00576

Connection 1: Ball head 28.5 mm

Construction use: Magnetic gripper

Size: 50/70



HTS-A3 D SGM 50/70 OP

Part no...:10.01.17.00583

Connection 1: Ball head 28.5 mm

Construction use: Magnetic gripper

Size: 50/70

Shape: Double block



HPS-SGM 2M8 50/70 OP

Part no...:10.01.17.00653

Construction use: Magnetic gripper

Connection 1: 2x screws M8

Size: 50/70

Shape: One-piece

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Magnetic gripper

SGM 70 G1/4-IG

Part no...:10.01.17.00165

<https://www.schmalz.com/10.01.17.00165>



STV-GE G1/8-AG 6

Part no...:10.08.02.00204

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 11.4 mm

Length L: 16.4 mm



STV-W G1/8-AG 6

Part no...:10.08.02.00158

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 20.1 mm



VSL 6-4 PU MI-TR

Part no...:10.07.09.00002

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C

Spare parts

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Magnetic gripper

SGM 70 G1/4-IG

Part no...:10.01.17.00165

<https://www.schmalz.com/10.01.17.00165>



REIB-RING SGM 70 PU-55

Part no...:10.01.17.00139

Construction use: Magnetic gripper

Size: 70

External diameter D: 68 mm

Internal diameter d: 51 mm