

Bell suction cup (round)

SAX 30 ED-85 M10-AG

Part no.: 10.01.19.00220

<https://www.schmalz.com/10.01.19.00220>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bell-Shaped Suction Cups SAX > SAX 30 ED-85 M10-AG

Bell suction cup (round) for best adaptation to strongly curved surfaces



Size: 30


Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Connection: M10-M

Number of folds: 0

Design Data



Attribute	Value
dn	4.10 mm
Dmax(S)	35.20 mm
Ds	31.70 mm
G1	M10-M
H	26 mm
LG1	14.50 mm
SW1	22 mm
Z (Stroke)	4.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	39 N
Lateral force	38 N
Lateral force (oily surface)	41 N
Volume	3.20 cm ³
Curve radius (min) (convex)	18 mm
Size	30
Connection	M10-M
Number of folds	0

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Bell suction cup (round)

SAX 30 ED-85 M10-AG

Part no.:10.01.19.00220

<https://www.schmalz.com/10.01.19.00220>

Suction cup material	Elastodur ED
Material hardness [Shore A]	85 Shore A
Weight	33 g
Product family	SAX