

Bell suction cup (oval)

SAOXM 60x20 ED-85 SC045-AR

Part no.:10.01.24.00001

<https://www.schmalz.com/10.01.24.00001>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > SAOXM 60x20 ED-85 SC045-AR

High-Speed bell shaped suction cup




Dimensions (LxB): 60 x 20

Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Design Data



Attribute	Value
Bk	20 mm
Bmax(S)	24 mm
Bs	18.70 mm
d	12.80 mm
H	21.90 mm
H2	3 mm
Lk	60 mm
Ls	61.80 mm
Z (Stroke)	4.50 mm

Technical Data

Attribute	Value
Lateral force	44 N
Lateral force (oily surface)	62 N
Volume	5 cm ³
Curve radius (min) (convex)	10 mm
Hose diameter (rec.) d	4 mm
Nipple family	SC 045-AR
Dimensions (LxB)	60 x 20
Suction cup material	Elastodur ED

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Bell suction cup (oval)

SAOXM 60x20 ED-85 SC045-AR

Part no...:10.01.24.00001

<https://www.schmalz.com/10.01.24.00001>

Material hardness [Shore A]	85 Shore A
Weight	7.20 g
Number of folds	0
Product family	SAOXM